



The FASTCAM SA6 has been developed to permit high definition recording and detailed high speed analysis of large spatial areas in applications such as automotive safety testing, fluid dynamics and solid mechanics. The system provides 1920x1440 pixel image resolution at all frame rates up to 1,125fps, 1920x1080 full HD resolution at frame rates up to 1,500fps and recording rates up to 75,000fps at reduced resolution.

The system utilizes a high performance CMOS image sensor to provide excellent light sensitivity allowing high speed recordings to be made with the minimum of additional lighting. The utilization of 12bit dynamic range output yields exceptional image quality and superior color fidelity. Photron's experience in the field of high quality broadcast imaging provides a stable camera operation and superior imaging performance.

The camera may be controlled via the optional remote local keypad or over a Gigabit Ethernet network, and is fully compatible with the Photron J-BOX for multiple camera installations. Integrated capping shutter to facilitate automated calibration and automated lens control options further extend the ease of system operation. The system is supplied with intuitive Photron FASTCAM Viewer (PFV) software and Photron Device Control SDK (software development kit) allowing integration with user specific software.

## **Target applications include:**

Automotive safety testing
Solid Mechanics (DIC)

Gulla

Fluid dynamics (PIV)Defense and aerospace research



## Benefits

- Performance examples:
  - 1,125 fps at 1920x1440 pixel resolution
  - 1,500 fps at 1920x1080 pixel resolution
  - 2,000 fps at 1280x1024 pixel resolution
  - 3,000 fps at 1024x768 pixel resolution
  - 5,000 fps at 768x512 pixel resolution
- Low noise, high quality imaging and superior color fidelity
- Composite and HD SDI video output for real time monitoring during set-up, recording and playback
- Options to enhance system operation include remote keypad with integrated viewfinder, integrated calibration shutter and automated lens control options and Nikon G type lenses
- GigaBit Ethernet interface and compatibility with Photron J-BOX for multiple camera installations





| FRAME RATE | MAXIMUM RESOLUTION |          | MAXIMUM<br>SHUTTER SPEED | RECORD DURATION (12-BIT) |       |        |         |           |           |
|------------|--------------------|----------|--------------------------|--------------------------|-------|--------|---------|-----------|-----------|
|            |                    |          |                          | TIME (Sec.)              |       |        | FRAMES  |           |           |
| (fps)      | Horizontal         | Vertical | SHUTTER SPEED            | 8GB                      | 16GB  | 32GB   | 8GB     | 16GB      | 32GB      |
| 50         | 1,920              | 1,440    |                          | 38.72                    | 77.54 | 155.22 | 1,936   | 3,877     | 7,761     |
|            | 1,920              |          |                          | 32.26                    | 64.61 | 129.35 |         | 3,877     |           |
| 125        | 1,920              | 1,440    |                          | 15.48                    | 31.01 | 62.08  | 1,936   | 3,877     | 7,761     |
| 250        | 1,920              |          |                          |                          |       |        |         | 3,877     |           |
| 500        | 1,920              | 1,440    |                          | 3.87                     | 7.75  | 15.52  | 1,936   | 3,877     | 7,761     |
|            | 1,920              |          |                          | 1.72                     |       | 6.89   |         | 3,877     |           |
| 1,500      | 1,920              | 1,080    | 2.76 µs                  | 1.72                     | 3.44  | 6.89   | 2,581   | 5,170     | 10,348    |
| 2,000      |                    |          | 2.70 µ3                  |                          |       |        | 4,356   | 8,725     |           |
| 3,000      | 1,024              | 768      | 1/367,000 sec            | 2.42                     | 4.84  | 9.70   | 7,260   | 14,542    | 29,105    |
| 4,000      |                    |          |                          |                          |       |        | 8,712   |           | 34,926    |
| 4,500      | 1,024              | 512      |                          | 2.42                     | 4.84  | 9.70   | 10,890  | 21,813    | 43,658    |
| 5,000      |                    |          |                          |                          | 5.81  |        |         | 29,084    | 58,211    |
| 8,000      | 512                | 384      |                          | 3.63                     | 7.27  | 14.55  | 29,041  | 58,168    | 116,423   |
| 12,000     |                    | 256      |                          | 3.63                     |       |        | 43,562  |           | 174,634   |
| 25,000     | 256                | 128      |                          | 6.97                     | 13.96 | 27.94  | 174,250 | 349,013   | 698,538   |
|            |                    |          |                          |                          |       |        | 348,501 | 698,026   |           |
| 75,000     | 256                | 32       |                          | 9.29                     | 18.61 | 37.25  | 697,002 | 1,396,053 | 2,794,154 |

|                            | Sensor                    | $10\mu m$ pixels, temperature stabilized, 12-bit ADC (Bayer system color, single sensor ) with micro lenses   | Phase Lock               | Enable cameras to sy master camera or ext                  |  |
|----------------------------|---------------------------|---|--------------------------|--|--|
| Shutter                    |                           | Global electronic shutter from 16.7ms to $2.76\mu\text{s}$ independent of frame rate  | Event Markers            | Ten user entered ever<br>the image sequence i              |  |
| Lens Mount                 |                           | Interchangeable F-mount, C-mount using supplied adapters,<br>Nikon G lens mount (optional), PL lens mount (optional), B4                                  |                          | through software   |  |
|                            |                           | lens mount (optional)   | Dual Speed<br>Recording  | Enables the recording factor of 2, 4 or 8 du               |  |
|                            | Extended Dynamic<br>Range | Selectable in twenty steps (0 to 95% in 5% increments) to prevent pixel over-exposure   | Trigger Modes            | Start, End, Center, Ma<br>Center, Random Man               |  |
|                            | Memory                    | 8GB (standard: 1,936 frames @ maximum resolution)<br>16GB (option: 3,877 frames @ maximum resolution)<br>32GB (option: 7,761 frames @ maximum resolution) | Saved Image<br>Formats   | JPEG, AVI, TIFF, BMP,<br>be saved with or with             |  |
|                            | Video Output              | Live and playback video through Dual HD-SDI or Single RS-170<br>(NTSC/PAL) outputs. Ability to zoom, pan and tilt within image<br>via keypad              | Data Display             | Frame Rate, Shutter S<br>Status (Playback/Re<br>Resolution |  |
| Camera Control             |                           |   | Partitioning             | Up to 64 memory seg  |  |
|                            |                           | Through Optional keypad with integrated viewfinder and Gigabit<br>Ethernet or RS-422  | Data Acquisition         | Supports Photron MC  |  |
|                            | User Preset               | Four user schedulable camera function controls mounted on the   | Cooling                  | Actively cooled  |  |
| Switches<br>Low Light Mode |                           | camera's rear panel<br>Low light mode drops the frame rate and shutter time to their<br>maximum values, while maintaining other set parameters, to        | Operating<br>Temperature | 0 - 40 degrees (32 -                                       |  |
|                            |                           | enable users to position and focus the camera   | Mounting                 | 1 x 1/4 - 20 UNC, 1  |  |
|                            | Triggering                | Selectable positive or negative TTL 5Vp-p or switch closure   | Dimensions               | 165mm (6.5")H×15   |  |
|                            | Trigger Delay             | Programmable delay on selected input and output triggers, 100ns resolution  | Weight                   | 15.21 lbs (6.9 kg)   |  |
|                            | Timing                    | Internal clock or external source   | Power<br>Requirements    | 100V-240V AC $\sim$ 1 DC operation 18-36                   |  |
|                            |                           |   |                          |  |  |

| hase Lock                | Enable cameras to synchronized precisely together to a master camera or external source   |
|--------------------------|---|
| Event Markers            | Ten user entered event markers mark specific events within<br>the image sequence in real time. Immediately accessible<br>through software |
| Dual Speed<br>Recording  | Enables the recording speed to be changed up or down by a factor of 2, 4 or 8 during a recording  |
| Frigger Modes            | Start, End, Center, Manual, Random, Random Reset, Random Center, Random Manual and Dual Speed Recording                                   |
| Saved Image<br>Formats   | JPEG, AVI, TIFF, BMP, RAW, PNG, MOV and FTIF. Images can be saved with or without image or comment data                                   |
| Data Display             | Frame Rate, Shutter Speed, Trigger Mode, Date or Time,<br>Status (Playback/Record), Real Time, Frame Count and<br>Resolution              |
| Partitioning             | Up to 64 memory segments for multiple recording in memory   |
| Data Acquisition         | Supports Photron MCDL and DAQ   |
| Cooling                  | Actively cooled   |
| Operating<br>Temperature | 0 - 40 degrees (32 - 104 degree F)  |
| Nounting                 | 1 x 1/4 - 20 UNC, 1 x 3/8 - 16 UNC, 6 x M6  |
| Dimensions               | 165mm (6.5")H×153mm (6.02")W×250mm (9.84")D   |
| Neight                   | 15.21 lbs (6.9 kg)  |
| Power<br>Requirements    | 100V-240V AC ~ 1.5A, 50-60Hz<br>DC operation 18-36 VDC, 100VA   |

**PHOTRON USA, INC.** 9520 Padgett Street, Suite 110 San Diego, CA 92126-4446 USA Tel: 858.684.3555 or 800.585.2129 Fax: 858.684.3558 Email: image@photron.com www.photron.com

PHOTRON (EUROPE) LIMITED The Barn, Bottom Road West Wycombe, Bucks, HP14 4BS United Kingdom Tel: +44 (0) 1494 481011 Fax: +44 (0) 1494 487011 Email: image@photron.com www.photron.com

**PHOTRON LIMITED** Fujimi 1-1-8 Chiyoda-Ku, Tokyo 102-0071 Japan Tel: +81 (0) 3 3238 2107 Fax: +81 (0) 3 3238 2109 Email: image@photron.co.jp www.photron.co.jp

### Specifications subject to change without notice

# Photron